

**Part No:** 3765-908

**Fabricated DWV**

**Glue-on Saddles**

**Desc:** 24X8 PVC STUB SADDLE SOC SCH40 N.P.R.

**MSRP:** 438.87

**Part Code:** 390

**Weight(lbs):** 15.521

**Weight(kg):** 7.04

**Weight(gm):** 7040


**Size:** 24 X 8

**Color:** WHITE

**Material:** PVC

**Schedule** SCH 40 DWV Stub Saddle

**Connection** Socket



**H** = 19-9/16

**L** = 17

**M** = 9-1/4

**N** = 3-5/16

## Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.
- L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.
- M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.
- N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.
- W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

