

**Part No:** 3777-788

**Fabricated DWV**

**Combo Wye & 1/8 Bend**

**Desc:** 18X8PVC RD CMB Y&1/8BND SOC SCH40

**MSRP:** 2156.49

**Part Code:** 390

**Weight(lbs):** 80.028

**Weight(kg):** 36.3

**Weight(gm):** 36300


**Size:** 18 X 8

**Color:** WHITE

**Material:** PVC

**Schedule** SCH 40 DWV- Reducing

**Connection** Socket x Socket x Socket



**G2** = 20-15/16

**G3** = 20-9/16

**H** = 24-5/8

**L** = 40-3/4

**M** = 19-1/8

**M1** = 9-3/8

**G1** = 1-13/16

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

