



Dealers Industrial Equipment

No.:

Date: 13-SEP-2016

### DATA SHEET Three-phase induction motor - Squirrel cage rotor

Customer :  
Product line : W22 Cooling Tower Motors: NEMA Premium - TEAO

Frame : 182/4T  
Output : 5 HP  
Frequency : 60 Hz  
Poles : 4  
Full load speed : 1755 rpm  
Slip : 2.50 %  
Voltage : 208-230/460 V  
Rated current : 14.3-12.9/6.45 A  
Locked rotor current : 96.8/48.4 A  
Locked rotor current (I<sub>L</sub>/I<sub>n</sub>) : 7.5  
No-load current : 6.40/3.20 A  
Full load torque : 14.8 lb.ft  
Locked rotor torque : 230 %  
Breakdown torque : 320 %  
Design : B  
Insulation class : F  
Temperature rise : 80 K  
Locked rotor time : 15 s (hot)  
Service factor : 1.25  
Duty cycle : S1  
Ambient temperature : -20°C - +40°C  
Altitude : 1000 m  
Degree of Protection : IP55  
Approximate weight : 95 lb  
Moment of inertia : 0.40033 sq.ft.lb  
Noise level : 56 dB(A)

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	6207 2RS	6206 2RS	100%	0.80	89.5
Regreasing interval	---	---	75%	0.74	89.5
Grease amount	---	---	50%	0.62	88.5

Notes:  
Downloaded from <http://dealerselectric.com>  
Generated for Model #00518AT3ECT184TF1-W2

Performed by

Checked