

**Part No:** 3929-628

**Fabricated DWV**

**Couplings**

**Desc:** 10X8 PVC RED COUPLING SOC SCH80

**MSRP:** 274.23

**Part Code:** 400

**Weight(lbs):** 11.371

**Weight(kg):** 5.158

**Weight(gm):** 5158


**Size:** 10 X 8

**Color:** GRAY

**Material:** PVC

**Schedule** SCH 40 DWV - Reducing

**Connection** Socket x Socket



**L** = 13-1/4

**M** = 11-3/4

**M1** = 9-5/8

**N** = 3-3/4

## Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.
- L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.
- M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.
- N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.
- W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

