

**Part No:** 3965-694C

**Fabricated CPVC Schedule 80 Glue on Saddles  
DWV**

**Desc:** 14X4 CPVC STUB SADDLE SOC SCH80 N.P.R.

**MSRP:** 516.53

**Part Code:** 099

**Weight(lbs):** 5.558

**Weight(kg):** 2.521

**Weight(gm):** 2521


**Size:** 14 X 4

**Color:** GRAY

**Material:** CPVC

**Type** Stub Saddle

**Connection** IPS O.D. X Socket



**N** = 3-7/8

**H** = 13-1/8

**L** = 12

**M** = 5-3/16

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

