

**Part No:** 3975-912C

**Fabricated CPVC Schedule 80 Wyes  
DWV**

**Desc:** 24X12 CPVC RED WYE SOC SCH80 N.P.R.

**MSRP:** 26024.21

**Part Code:** 099

**Weight(lbs):** 369.59

**Weight(kg):** 167.643

**Weight(gm):** 167643


**Size:** 24 X 12

**Color:** GRAY

**Material:** CPVC

**Type** Reducing

**Connection** Socket x Socket x Socket



**H2** = 40-3/4

**G3** = 29

**H3** = 35-1/4

**L** = 57-1/2

**M** = 26-7/16

**M1** = 14-1/8

**H1** = 16-3/4

**G1** = 4-3/4

**G2** = 28-3/4

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

