

**Part No:** 3976-668

**Fabricated DWV**

**Double Wye**

**Desc:** 12X8 PVC RD DBL Y SOC SCH80 N.P.R

**MSRP:** 1490.42

**Part Code:** 400

**Weight(lbs):** 64.582

**Weight(kg):** 29.294

**Weight(gm):** 29294

**Size:** 12 X 8


**Color:** GRAY

**Material:** PVC

**Schedule** SCH 80 DWV

**Type** Reducing

**Connection** Socket x Socket x Socket x Socket



**H1** = 10-1/2

**H2** = 23-1/4

**H3** = 22-13/16

**L** = 33-3/4

**M** = 14-1/8

**M1** = 9-5/8

**G1** = 4-1/4

**G2** = 17

**G3** = 18-9/16

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

