



Dealers Industrial Equipment

No.:

Date: 13-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Close Coupled Pump : Three-Phase - "JM" Type - ODP - High Efficiency

Frame : 213/5JM
Output : 7.5 HP
Frequency : 60 Hz
Poles : 4
Full load speed : 1755 rpm
Slip : 2.50 %
Voltage : 575 V
Rated current : 7.52 A
Locked rotor current : 50.4 A
Locked rotor current (I_L/I_n) : 6.7
No-load current : 3.28 A
Full load torque : 22.1 lb.ft
Locked rotor torque : 180 %
Breakdown torque : 250 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 8 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP21
Approximate weight : 72 lb
Moment of inertia : 0.91977 sq.ft.lb
Noise level : ---

	D.E.	N.D.E.
Bearings	6209 ZZ	6206 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.83	88.5
75%	0.78	88.5
50%	0.68	87.5

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #00718OP3H213JM

Performed by

Checked