

Schedule 80 PVC Industrial Products & Accessories
Diaphragm Check Valves & PVC In-line Adjustable Spring Check Valves



Diaphragm Check Valves



Pressure Rating @ 73°F (23°C), Water
 Full Flow (open) 150 psi
 Back Pressure (closed) 100 psi
 Maximum Service Temperature
 PVC = 140°F (60°C)
 Temperature/Pressure De-ratings Apply
 Santoprene™ TPE Seat

PVC Diaphragm Check Valves - Socket

Part Number	Size	Std Pk	Mstr Ctn	Disc Code	Price Each
6562-007	3/4	15	0	004	84.64

PVC Diaphragm Check Valves - Thread

Part Number	Size	Std Pk	Mstr Ctn	Disc Code	Price Each
6561-007	3/4	15	0	004	84.64

PVC In-line Adjustable Spring Check Valves



Fipt x Mipt



Mipt x Fipt



Fipt x Fipt



Pressure Rating @ 73°F (23°C), Water
 200 psi
 Maximum Service Temperature
 PVC = 140°F (60°C)
 Temperature/Pressure De-ratings Apply

2 - 14 lbs. Adjustable Spring Tension
 (5 to 32 feet of head)
 Factory Preset to Approx. 5 psi
 (12 feet of head)
 Each full turn of adjustment nut = 1 psi
 (2.3 feet of head)
 Stainless Steel Adjustment Hardware
 EPDM Seat

Standard Unit - Female Inlet x Male Outlet

Part Number	Size	Std Pk	Mstr Ctn	Disc Code	Price Each
-------------	------	--------	----------	-----------	------------

Fipt x Mipt (Inlet x Outlet)

S1102-05	1/2	30	180	026	10.40
S1102-07	3/4	25	150	026	10.64
S1102-10	1	25	150	026	17.66
S1102-05-07	1/2X3/4	25	150	026	15.18

Male Inlet x Female Outlet Option

Part Number	Size	Std Pk	Mstr Ctn	Disc Code	Price Each
-------------	------	--------	----------	-----------	------------

Mipt x Fipt (Inlet x Outlet)

S1101-05	1/2	30	180	026	10.40
----------	-----	----	-----	-----	-------

Female Inlet x Female Outlet Option

Part Number	Size	Std Pk	Mstr Ctn	Disc Code	Price Each
-------------	------	--------	----------	-----------	------------

Fipt x Fipt (Inlet x Outlet)

S1100-07	3/4	25	150	026	10.99
----------	-----	----	-----	-----	-------