

**Part No:** 801-668C

**Schedule 80 PVC & CPVC**

**Tee**

**Desc:** 12X8 CPVC RED TEE SOC SCH80

**MSRP:** 5479.92

**Part Code:** 091

**Weight(lbs):** 44.04

**Weight(kg):** 19.976

**Weight(gm):** 19976


**Size:** 12"X12"X8"

**Color:** GRAY

**Material:** CPVC

**Connection** Socket x Socket x Socket

**Type** Reduction



**G** = 4-7/8

**G1** = 7-1/8

**M1** = 9-3/4

**M2** = 14-1/4

**G2** = 4-7/8

**H** = 11-15/32

**H1** = 11-5/32

**H2** = 11-15/32

**L** = 22-29/32

**M** = 14-1/4

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

