

Part No: 835-005SR

Schedule 80 PVC & CPVC Adapter

Desc: 1/2 PVC FEMALE ADAPTER SOCXSRFPT SCH80

MSRP: 5.21

Weight(lbs): 0.062

Size: 1/2"

Part Code: 086

Weight(kg): 0.028


Weight(gm): 28

Color: GRAY

Material: PVC

Connection Socket x SR Fipt

Type Standard



L = 1-23/32

M = 1- 5/32

M1 = 1- 3/16

N = 3/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

