



Dealers Industrial Equipment

No.:

Date: 23-SEP-2016

DATA SHEET Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : W22 Super Premium

Frame : 254/6T
Output : 15 HP
Frequency : 60 Hz
Poles : 4
Full load speed : 1775 rpm
Slip : 1.39 %
Voltage : 208-230/460 V
Rated current : 39.4-35.6/17.8 A
Locked rotor current : 303/151 A
Locked rotor current (I_L/I_n) : 8.5
No-load current : 16.0/8.00 A
Full load torque : 43.8 lb.ft
Locked rotor torque : 280 %
Breakdown torque : 330 %
Design : A
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 20 s (hot)
Service factor : 1.25
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 280 lb
Moment of inertia : 3.6561 sq.ft.lb
Noise level : 64 dB(A)

	D.E.	N.D.E.
Bearings	6309 C3	6209 C3
Regreasing interval	20000 h	20000 h
Grease amount	13 g	9 g

Load	Power factor	Efficiency (%)
100%	0.83	93.6
75%	0.76	93.0
50%	0.66	91.7

Notes:
Downloaded from <http://dealerselectric.com>
Generated for Model #01518EG3E254T-W22

Performed by

Checked