

**Part No:** FCKV-030

**Flanges & Cut-In Kit**

**Flange Cut-In Kit**

**Desc:** 3 PVC FLANGE CUT-IN KIT FKM

**MSRP:** 939.76

**Part Code:** 017

**Weight(lbs):** 8.768


**Weight(kg):** 3.977

**Weight(gm):** 3977

**Size:** 3

**Color:** GRAY

**Material:** PVC



**H =** 4

**L =** 5-7/8

**M =** 7-9/16

**Type** Kit

**Pressure Rating** 150 psi @ 73° F

**Gasket** FKM

## Injection Molded Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.
- H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch
- L** = Overall length of fittings; ± 1/16 inch.
- M** = Outside diameter of socket/thread hub; ± 1/16 inch.
- N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.
- W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

