



Dealers Industrial Equipment

No.:

Date: 23-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : W22 Oil Well Pumping : High Slip - NEMA Design "D" - TEFC (IP55)

Frame : 324/6T
Output : 25 HP
Frequency : 60 Hz
Poles : 6
Full load speed : 1125 rpm
Slip : 6.25 %
Voltage : 208-230/460 V
Rated current : 66.7-62.4/31.2 A
Locked rotor current : 362/181 A
Locked rotor current (I_L/I_N) : 5.8
No-load current : 25.0/12.5 A
Full load torque : 115 lb.ft
Locked rotor torque : 300 %
Breakdown torque : 0 %
Design : D
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 16 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 523 lb
Moment of inertia : 10.412 sq.ft.lb
Noise level : 62 dB(A)

	D.E.	N.D.E.
Bearings	6312 C3	6212 C3
Regreasing interval	20000 h	20000 h
Grease amount	21 g	13 g

Load	Power factor	Efficiency (%)
100%	0.84	88.5
75%	0.79	88.5
50%	0.69	85.5

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #02512ES3EOW324T-W22

Performed by

Checked