

# Product data sheet

Specifications

SQUARE D

Green Premium™



## Mini circuit breaker, QOU, 10A, 1 pole, 120/240VAC, 10kA

QOU110

Product availability : Stock - Normally stocked in distribution facility

**Price\* : 40.20 USD**

### Main

Product or Component Type	Miniature circuit-breaker
Range of Product	QOU
Circuit breaker type	Standard
Circuit breaker application	HACR rated

### Complementary

Line Rated Current	10 A
Electrical connection	Slotted box lugs, line side Slotted box lugs, load side
[Ue] rated operational voltage	120/240 V AC 120 V AC 48 V DC
Mounting Mode	Unit mount
AWG gauge	AWG 14...AWG 2 aluminium/copper
Height	4.05 in (102.87 mm)
Width	0.75 in (19.05 mm)
Depth	2.95 in (74.93 mm)
Tightening torque	45 lbf.in (5.08 N.m) (AWG 14...AWG 2)

### Environment

Product Certifications	IEC CSA UL Listed
------------------------	-------------------------

### Ordering and shipping details

Category	00900-QOU BREAKERS & SWITCH
Discount Schedule	DE2
GTIN	785901205678
Returnability	Yes
Country of origin	MX

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	3.10 in (7.874 cm)
Package 1 Length	4.50 in (11.43 cm)
Package 1 Weight	6.40 oz (181.437 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	66
Package 2 Height	3.30 in (8.382 cm)
Package 2 Width	14.00 in (35.56 cm)
Package 2 Length	20.90 in (53.086 cm)
Package 2 Weight	24.75 lb(US) (11.226 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	2772
Package 3 Height	40.00 in (101.6 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	1014.00 lb(US) (459.942 kg)


## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	<a href="#">Yes</a>
Halogen content performance	Halogen free product


## Contractual warranty

Warranty	18 months
----------	-----------

**Dimensions**



2.50 [64] MIN. WIRE BENDING SPACE FOR 2 AWG  
 1.50 [38] MIN. WIRE BENDING SPACE FOR 14 AWG  
 TYP. BOTH ENDS FOR ALL CB'S SHOWN PER ARTICLE 430-1-(B) NEC



**Recommended replacement(s)**