



Actual

Catalog Number: 13-2423
Product ID: 7TAA008010R0049
UPC Number: 78378600453
Status: A

Cable Tie Natural Polyamide (nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support Length of 302mm (11.9 Inches) Width of 4.6mm (0.18 Inch) Thickness of 1.2mm (0.046 Inch) Tensile Strength Rating of 220 Newtons (50 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Standard
Application	For Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications
Standard	UL E49405
Width	0.18 in ; 4.6 mm
Length	11.9 in ; 302 mm
Thickness	0.046 in ; 1.2 mm
Material	Polyamide/Nylon 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	50 pounds ; 222 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.6mm
Length belt/tape/tie	302mm
Tie thickness	1.2mm
Min. holding force	222N
Model	Internal tothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	50
Inner Dimensions (inches)	15x1x5
Outer Quantity	500
Weight Uom	5 lbs. per 1000