



Actual

Catalog Number: 5345SST6-6
Product ID: 7TAD012420R0147
UPC Number: 78621008069
EAN Number: 05415022450217
Status: Active

1-1/4 Inch Liquidtight Fitting for Flexible Metallic Conduit, 45 Degree, High UV Resistance, NEMA Ratings: 3, 3R, 4, 4X, Length 3.90 Inches/99.06mm, Width 2.25 Inches/57.15mm, Height 2.86 Inches/72.64mm, Temperature Range 0 to 105 Degrees C, 316 Stainless Steel Body and Ground Cone

Corrosive environments can cause traditional metallic fittings to corrode and require replacement. The new stainless steel T&B Liquidtight Fittings are constructed of type 316 stainless steel to resist corrosion, all while offering high strength, UV resistance, and extreme performance up to 105 Degrees Celsius.

- NEMA Ratings: 3, 3R, 4, 4X
- Ideal for Food and Beverage, Pharmaceutical, Petrochemical, Wastewater Processing, Salt Water and Other Corrosive Environments

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B Industrial Fitting
Type	45 Degree Fitting for Flexible Metallic Conduit
Special Features	Stronger and More UV-resistant than Nonmetallic Fittings
Application	Connects Flexible Metallic Liquidtight Conduit to a Box or Enclosure
Size	1-1/4 Inch
Connection	45 Degree
Material	316 Stainless Steel Body and Ground Cone
Finish	None
Color	Metallic
NEMA Rating	3, 3R, 4, 4X
Insulation	Y
Temperature Rating	105 Degrees C

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Stainless steel
Surface protection	Untreated
Total length	99.06mm
Total height	72.64mm
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	N
	N

Approved in combination with protective
conduit UL

Approved in combination with protective N
conduit FI

Operating temperature 0-105°C

Packaging

Inner Quantity 5

Inner Dimensions (inches) 9.5x6.5x4.5

Outer Quantity 25

Outer Dimensions (inches) 23.31x6.81x9.81

Weight Uom 1.01 lbs. Each

Documents / Support Tools

3D Rendering Available on Website

Technical Drawing / Data Sheet TDS000126

Technical Drawing / Data Sheet Canada TDS000126

Instruction Sheet TA05037-TB2

Support/Tools Available on Website

Marketing Brochure US Available on Website