




1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: info@wescomfg.com

PART NO. 261023, 24" X 24" PLATFORM FIXED BASE POWERED STACKER



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Battery and charger included.
- 110V AC models available. (Special order, NO cancellations or returns.)
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261023

110V AC Powered #261023AC

- Meets ANSI B56.10 specifications.
- Power Drive option available.

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#) | [Stacker Low Profile Outtrigger Option](#)

Video



Specifications



PART NUMBER	261023
MODEL	PESPL-68-2424
TYPE	24" x 24" Platform Models
FRONT WHEEL	(2) 5" Phenolic
REAR SWIVEL CASTER	(2) 4" Phenolic
LIFT HEIGHT	68"
CAPACITY	1000 lb
PLATFORM WIDTH	24"
PLATFORM LENGTH	24"
LOAD CENTER	15"
LOWERED HEIGHT	5.75"
BASE LEG (ID/OD)	15"/21"
OVERALL WIDTH	25.5"
OVERALL HEIGHT	80"
OVERALL DEPTH	36"
WEIGHT	428 lb
MADE IN THE USA	

5th Wheel Steering Option

5TH WHEEL STEERING OPTION




5th Wheel Steering Option for easier mobility & precision steering in confined areas
Available only on 1,500 and 2,000 lb models.
8" locking polyurethane wheels. Spring loader handle. Can be field installed.
Order as separate option under Part # 261099

Look

5th wheel steering option

Stacker Low Profile Outrigger Option

STACKER LOW PROFILE OUTRIGGER OPTION



Stacker Low Profile Outrigger Option