



Catalog Number: BEM-0751
Product ID: 7TCA303080R0055
UPC Number: 78621013830
EAN Number: 05415022403534
Status: A



Actual

EMC Cable Gland, Thread Size 3/4 Inch NPT, Cable Range 10 to 18mm, Shield Range 7 to 14mm, Thread Length 15mm, Nickel Plated Brass

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance
- Extended radial contact with the shielding for improved EMI protection

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	EMC Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	3/4 Inch NPT
Conductor Range	10 to 18 Millimeters
Material	Brass
Finish	Nickel Plated
Color	Metallic
NEMA Rating	4
Temperature Rating	-20 to +100 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	15mm
Suitable for cable diameter	10 - 18mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C
EMC-version	Y

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	20
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000033
Instruction Sheet	TA05286-TB2
Support/Tools	Available on Website

Header



3D Model

Available on Website