



Actual

Catalog Number: BEM-M632
Product ID: 7TCA303080R0050
UPC Number: 78621013825
EAN Number: 05415022403480
Status: Active

EMC Cable Gland, Thread Size M63, Cable Range 37 to 53 Millimeters, Shield Range 33 to 49 Millimeters, Thread Length 10 Millimeters, Nickel Plated Brass

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance
- Extended radial contact with the shielding for improved EMI protection

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	EMC Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	M63
Conductor Range	37 to 53 Millimeters
Material	Brass
Finish	Nickel Plated
Color	Metallic
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	63
Pitch thread	1.5mm
Thread length	10mm
Suitable for cable diameter	37 - 53mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C
EMC-version	Y

Packaging

Inner Quantity	2
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	2
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000033
Technical Drawing / Data Sheet Canada	TDS000033
Instruction Sheet	TA05286-TB2

Support/Tools

Available on Website

Thomas & Betts - USA