



Catalog Number: CPO2000-2-A
Product ID: 7TAA017980R0044
UPC Number: 78620987373
Status: A



Actual

Thin-Wall Heat Shrinkable Tubing, Red Cross-Linked Polyolefin, 2 Inch, Shrink Ratio 2:1, Length 4 Feet, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heat Shrinkable Tubing
Shrink Ratio	2:1
Length	4 ft ; 1.22 m
Dielectric Strength	600 V/Mil (24kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 to +275 F ; -55 to +135 C
Minimum Shrink Temperature	248 F ; 120 C
Flammability	Flame Retardant
Water Absorption	0.20%
Color	Red

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	51mm
Inner diameter after heat-shrink	25.4mm
Nominal diameter inch	2 inch
Wall thickness after shrinking	1.143mm
Length	1.22m
Operation temperature	-55-+135°C
Colour	Red
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Inner Quantity	10
Inner Dimensions (inches)	13x13x3
Outer Quantity	100
Outer Dimensions (inches)	13x13x6
Weight Uom	3.13 lbs. per 100