



**Catalog Number:** CPO250-0-1.000  
**Product ID:** 7TAA017980R0046  
**UPC Number:** 78621083406  
**Status:** A



Thin-Wall Heat Shrinkable Tubing, Black Cross-Linked Polyolefin, 1/4 Inch, Shrink Ratio 2:1, Length 1 Inch, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

Actual

#### North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heat Shrinkable Tubing
Shrink Ratio	2:1
Length	1 in ; 25.4 mm
Dielectric Strength	600 V/Mil (24kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 to +275 F ; -55 to +135 C
Minimum Shrink Temperature	248 F ; 120 C
Flammability	Flame Retardant
Water Absorption	0.20%
Color	Black

#### European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	6.35mm
Inner diameter after heat-shrink	3.302mm
Nominal diameter inch	1/4 inch
Wall thickness after shrinking	0.508mm
Length	0.0254m
Operation temperature	-55-+135°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

#### Packaging

Outer Quantity	12000
Outer Dimensions (inches)	10.5x8.25x12.75
Weight Uom	0.55 lbs. per 1000

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------