



WESCO®
Industrial Products, Inc.

Wesco Industrial Products, Inc.

1250 Welsh Rd
North Wales, PA 19454
Phone: 800.445.5681 • **Fax:** 800.346.5511
Email: info@wescomfg.com

PART NO. 272744, DELUXE ADJUSTABLE FORK MODEL TRUCK



- Deluxe Models feature 5 year pump warranty and 5,500 lb. capacity
- Pump overload bypass.
- Rubber coated handle.
- 200° steering.
- Tapered fork tips.
- Adjustable fork tie rods.
- Exit rollers.
- 8 gauge 6" wide reinforced forks.
- 5 year pump warranty.
- US Patent No. 6,808,357.
- 7" non-marking moldon polyurethane steering wheel.
- 3" non-marking moldon polyurethane load wheels.
- 7.75" raised height.
- 3" lowered height.
- 6" wide forks.

Adjustable fork width can be set from 21" to 27" or anywhere in between. Just loosen and reset front and rear adjusting bolts. **A Wesco® exclusive!** Work of two!

[Video](#) | [Specifications](#)

Video



Specifications

PART NUMBER	272744
FORK DIMENSION	21"-27" x 46"
CAPACITY	5500 lb
W1	21" to 27"
L1	48"
W2	6"
L2	63"
WHL1	8"
WHL2	3"
H1	47"
H2	3"
H3	8"
WEIGHT	180 lb