



1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: [info@wescomfg.com](mailto:info@wescomfg.com)

## PART NO. 272943, CAPACITY POWER DRIVE STACKER



- Lift height of 98 1/4". Dual chain lift.
- Includes two, 12 volt, 187 AH, sealed batteries and a separate UL approved charger.
- Power propulsion system takes the effort out of moving heavy loads. Also provides easy steering.
- Fingertip control provides variable forward and reverse speeds.
- Automatic safety stop on top of control post. Unit shuts down when safety stop comes into contact.
- Load wheels, steering wheel and drive wheel are all moldon polyurethane.
- Adjustable forks.
- 6 month warranty on parts only.
- Cannot be used with pallets; only skids without bottom slats.

### Specifications

<b>PART NUMBER</b>	272943
<b>TYPE</b>	EKS-10
<b>CAPACITY</b>	2200 lb
<b>WIDTH FORKS</b>	5"
<b>LENGTH FORKS</b>	35.25"
<b>LOAD CENTER</b>	17.5"
<b>OVERALL WIDTH</b>	35"
<b>OVERALL HEIGHT</b>	70" to 117.5"
<b>OVERALL DEPTH</b>	64"
<b>WEIGHT</b>	826 lb
<b>BATTERY</b>	(2) 12 V 187 Ah



<b>ADJUSTABLE OUTSIDE FORK SPREAD</b>	12" to 29"
<b>LOWERED FORK HEIGHT IN STANDARD MODE</b>	2.6"
<b>RAISED FORK HEIGHT IN STANDARD MODE</b>	98.25"
<b>LOWERED HEIGHT OF MAST</b>	70"
<b>RAISED HEIGHT OF MAST</b>	117.5"