



Family

Catalog Number: G.PX.32SW
Product ID: 7TAA292910R0083
UPC Number: 78620995720
EAN Number: 07630030237591
Status: Active

Open Braided Hose, Self Winding - NW 32, Color Black

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	PMA
Type	Braided Hose
Special Features	UV Resistant; Free from Halogens
Application	Mechanical Protection
Trade Size	NW32
Length	25 m
Flexibility	Highly Flexible
Material	Polyester Monofil and Multifil Fibres
Color	Black

European Specifications (ETIM)

ETIM	EC001182 Braided hose
Nominal diameter	32mm
Bundle diameter	29-35mm
Material	Plastic
Material quality	Polyester (PET)
Halogen free	Y
Surface protection	Untreated
Colour	Black
Open (mountable afterwards)	Y
Temperature	-55 - +150°C
Fire resistance in accordance with UL94	V0
Approved according to UR	N
Approved according to DIN 5510	Y
Approved according to NF F 16-101	Y

Packaging

Inner Quantity	1
Outer Quantity	4
Outer Dimensions (inches)	30.709x23.622x19.685
Weight Uom	0.02 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com