



Actual

Catalog Number: HS30-40
Product ID: 7TAA017110R0004
UPC Number: 78621088183
EAN Number: 05414363135005
Status: A

Heavy-Wall Heat-Shrinkable Tubing for Cable Range 1500 - 2500 MCM, Expanded Diameter 4.72, Length 30 inch. rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Made of thermally stabilized cross-linked polyolefin, enabling a recovered wall thickness greater than that of the cable jacket replaced.
- Withstands severe mechanical requirements of U.R.D., submersible, and direct burial installations.
- Tubing, featuring an internally applied sealant, offers protection against moisture, and may be used over lead, steel, aluminum, copper, standard plastic and elastomeric insulating materials.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heavy-Wall Heat Shrinkable Tubing
Special Features	Made of thermally stabilized cross-linked polyolefin, enabling a recovered wall thickness greater than that of the cable jacket replaced.
Shrink Ratio	3:1
Voltage Rating	600 V
Length	30 in
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	3:1
Inner diameter before heat-shrink	119.888mm
Inner diameter after heat-shrink	38.608mm
Nominal diameter inch	Other
Wall thickness after shrinking	3.81mm
Length	0.762m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	4x48x4
Weight Uom	1.15 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000473
Safety Data Sheet (SDS) Global	SDS-00046-TB2

