



Representative

Catalog Number: HS4-30
Product ID: 7TAA017100R0008
UPC Number: 78621085821
EAN Number: 05414363135029
Status: A

Heavy-Wall Heat-Shrinkable Tubing for Cable Range 1 - 3/0 AWG, Expanded Diameter 1.1 inch, Length 5 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Made of thermally stabilized cross-linked polyolefin, enabling a recovered wall thickness greater than that of the cable jacket replaced.
- Withstands severe mechanical requirements of U.R.D., submersible, and direct burial installations.
- Tubing, featuring an internally applied sealant, offers protection against moisture, and may be used over lead, steel, aluminum, copper, standard plastic and elastomeric insulating materials.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heavy-Wall Heat Shrinkable Tubing
Special Features	Made of thermally stabilized cross-linked polyolefin, enabling a recovered wall thickness greater than that of the cable jacket replaced.
Standard	UL E9809
Voltage Rating	600 V
Length	5 in ; 127 mm
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	3:1
Inner diameter before heat-shrink	27.94mm
Inner diameter after heat-shrink	8.89mm
Nominal diameter inch	Other
Wall thickness after shrinking	3.048mm
Length	0.127m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	20
Outer Dimensions (inches)	6x6x6
Weight Uom	3.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000473
Instruction Sheet	TA01024-TB2
Safety Data Sheet (SDS) Global	SDS-00046-TB2

