



Representative

Catalog Number: HS500-1000
Product ID: 7TAA017090R0008
UPC Number: 78621085823
EAN Number: 05414363152910
Status: A

Heavy-Wall Heat-Shrinkable Tubing for Cable Range 500-1000 kcmil, Cross-linked Polyolefin with thermoplastic Adhesive Liner, Expanded Diameter 2 Inches, Length 9 Inches, 600V, Black

- Made of thermally stabilized cross-linked polyolefin, enabling a recovered wall thickness greater than that of the cable jacket replaced.
- Withstands severe mechanical requirements of U.R.D., submersible, and direct burial installations.
- Tubing, featuring an internally applied sealant, offers protection against moisture, and may be used over lead, steel, aluminum, copper, standard plastic and elastomeric insulating materials.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heavy-Wall Heat Shrinkable Tubing
Special Features	Made of thermally stabilized cross-linked polyolefin, enabling a recovered wall thickness greater than that of the cable jacket replaced.
Standard	UL E9809
Voltage Rating	600 V
Length	9 in ; 228.6 mm
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	3:1
Inner diameter before heat-shrink	50.8mm
Inner diameter after heat-shrink	16.002mm
Nominal diameter inch	2 inch
Wall thickness after shrinking	3.556mm
Length	0.2286m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	5
Outer Dimensions (inches)	9x6x12
Weight Uom	12.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000473
Instruction Sheet	TA01024-TB2
Safety Data Sheet (SDS) Global	SDS-00046-TB2
Catalog	Available on Website

