

Catalog Number: LBNEC7-G
Product ID: 7TAA087890R0256
UPC Number: 70450801516
Status: Active

PVC Coated Mogul Pulling Elbow, Size 2-1/2 Inch/63 Metric, 90 Degree Bend, Bending Radius 5 1/4, A 21-11/16 Inch, B-8 9/32 Inch, C 4-1/2 Inch, Gray

North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5746 Electrical conduit elbow
Brand Name	Ocal
Type	Mogul Pulling Elbow
Special Features	Large Dome Cover Permits Easy, Straight Through Pull
Application	To Provide an Accessible Weather Resistant Chamber for Containing Heavy Duty Conductors
Material	Aluminum Die Cast
Color	Gray
Finish	Aluminum Lacquer
Trade Size	2-1/2 Inch/63mm
Connection	90 Degree Bend

European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Other
Surface protection	Untreated
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	63mm
Angle of bow	90°

Packaging

Outer Quantity	1
Outer Dimensions (inches)	24.75x16.12x5.62
Weight Uom	1100 lbs. per 100

Documents / Support Tools

Catalog US	Available on Website
------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com