



Actual

Catalog Number: S20/10M
Product ID: 7TCA296010R0057
EAN Number: 05020963000584
Status: Active

Inherent Low Fire Hazard Steel Conduit, Nominal Conduit Size 20mm, Outside Diameter 20.5mm, Inside Diameter 16.9mm, Static Bend Radius 45mm, Reel Length 10 Meters, Galvanised Steel General Purpose

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Adaptaflex
Type	Low Fire Hazard Conduit
Special Features	Very High UV Protection and Fatigue Life
Application	Indoors / Outdoors - Light Industrial, Buildings
Trade Size	1/2 Inch
Outside Diameter	20.5mm
Inside Diameter	16.9mm
Length	10 m
Radius	45mm
Flexibility	Very High
Material	Galvanized Steel

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Outer diameter	20.5mm
Inner diameter	16.9mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	Not sheathed
Operating temperature	-50-+300°C
Degree of protection (IP)	IP40
Weight	0.236kg/m
Colour	Metallic
Bending strength	Flexible

Packaging

Outer Quantity	1
Outer Dimensions (inches)	16x17x16
Weight Uom	5.19 lbs. Each

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com