



Actual

Catalog Number: SPB25/25M
Product ID: 7TCA296040R0135
EAN Number: 05020963004469
Status: Active

Highly Flexible Steel Conduit, Nominal Conduit Size 25mm, Outer Diameter 26.0mm, Inner Diameter 21.4mm, Maximum Bend Radius 55mm, Reel Length 25 Meters, Galvanised Steel Core with PVC Jacket and Galvanised Steel Overbraid

- Very high UV resistance
- Medium flexibility
- Medium fatigue life
- High mechanical, high abrasion resistance
- Self extinguishing
- Enhanced EMI screen rate
- Security
- Lighting

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Adaptaflex
Type	High Flexibility Conduit
Special Features	Very High UV Protection
Application	Indoors / Outdoors - Enhanced EMI Screen - High Abrasion Resistance
Trade Size	3/4 Inch
Length	25 m
Radius	55mm
Flexibility	High
Material	Galvanized Steel Core and Overbraid with PVC Jacket

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Outer diameter	26mm
Inner diameter	21.4mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Sheathing material 2nd coating (exterior)	Steel wire, galvanized
Operating temperature	-15-+70°C
Degree of protection (IP)	IP54
Weight	0.28kg/m
Colour	Metallic
Bending strength	Flexible

Packaging

Inner Quantity	1
Inner Dimensions (inches)	48x40x50
Outer Quantity	5
Outer Dimensions (inches)	48x40x50
Weight Uom	38.91 lbs. Each

Header

3D Model

Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com