



Actual

**Catalog Number:** SPTC50/10M  
**Product ID:** 7TCA296100R0188  
**EAN Number:** 05020963018138  
**Status:** Active

Highly Flexible Conduit, 1-1/2 Inch, Nominal Conduit Size 50mm, Outside Diameter 56.0mm, Inside Diameter 48.4mm, Static Bend Radius 90mm, Reel Length 10 Meters, Galvanised Steel Core with PVC Jacket and Tinned Copper Overbraid, Black

- Very high UV resistance
- High flexibility
- Medium fatigue life
- High mechanical, high abrasion resistance
- Self extinguishing
- High EMI screen rate
- Machine Building
- External Safety Critical Areas
- Hospitals

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Adaptaflex
Type	High Flexibility Conduit
Special Features	Very High UV Protection
Application	Indoors / Outdoors - Enhanced EMI Screen - High Abrasion Resistance
Trade Size	1-1/2 Inch
Outside Diameter	56.0mm
Inside Diameter	48.4mm
Length	10 Meters
Radius	90mm
Flexibility	High
Material	Galvanized Steel Core, Tinned Copper Overbraid with PVC Jacket
Color	Black

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Outer diameter	56mm
Inner diameter	48.4mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Sheathing material 2nd coating (exterior)	Other
Operating temperature	-15-+70°C
Degree of protection (IP)	IP54
Weight	0.939kg/m
Colour	Black
Bending strength	Flexible

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	25.49 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)