



Actual

**Catalog Number:** SS20/10M  
**Product ID:** 7TCA296120R0018  
**EAN Number:** 05020963027284  
**Status:** Active

Inherent Low Fire Hazard Conduit, Nominal Conduit Size 20mm, Outside Diameter 20.5mm, Inside Diameter 16.9mm, Static Bend Radius 45mm, Reel Length 10 Meters, 316 Stainless Steel, Corrosion Resistant

- High UV resistance
- High flexibility
- High fatigue life
- Halogen free
- Inherent low fire hazard
- Marine
- Railway
- Corrosive Environments
- Food Industry

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Adaptaflex
Type	Low Fire Hazard Conduit
Special Features	Very High UV Protection and Fatigue Life
Application	Indoors / Outdoors - Corrosive Environments
Trade Size	1/2 Inch
Outside Diameter	20.5mm
Inside Diameter	16.9mm
Length	10 m
Radius	45mm
Flexibility	Very High
Material	Stainless Steel

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Outer diameter	20.5mm
Inner diameter	16.9mm
Material	Stainless steel
Surface protection	Untreated
Sheathing material 1st coating	Not sheathed
Operating temperature	-50-+350°C
Degree of protection (IP)	IP40
Weight	0.236kg/m
Colour	Metallic
Bending strength	Flexible

#### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	4.05 lbs. Each

#### Header

3D Model

Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)