



Actual

**Catalog Number:** SSB25/25M  
**Product ID:** 7TCA296100R0193  
**EAN Number:** 05020963011375  
**Status:** Active

Low Fire Hazard, High Flexibility, Covered Steel Conduit, Nominal Conduit Size 25mm, Outside Diameter 26.0mm, Inside Diameter 21.4mm, Static Bend Radius 55mm, Reel Length 25 Meters, 316 Stainless Steel Core and Overbraid

- Very high UV resistance
- High flexibility
- High fatigue life
- High mechanical strength, high abrasion resistance
- Inherent low fire hazard and halogen free
- Standard EMI screen rating
- Marine
- Corrosive Environments

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Adaptaflex
Type	Low Fire Hazard Conduit
Special Features	Very High UV Protection and High Fatigue Life
Application	Indoors / Outdoors - Standard EMI Screen - Very High Abrasion Resistance
Trade Size	3/4 Inch
Outside Diameter	26.0mm
Inside Diameter	21.4mm
Length	25 m
Radius	55mm
Flexibility	High
Material	Stainless Steel Core and Overbraid

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Outer diameter	26mm
Inner diameter	21.4mm
Material	Stainless steel
Surface protection	Untreated
Sheathing material 1st coating	Stainless steel wire
Operating temperature	-50-+300°C
Degree of protection (IP)	IP40
Weight	0.23kg/m
Colour	Metallic
Bending strength	Flexible

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	12.68 lbs. Each

### Header

3D Model	Available on Website
----------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)