

**Catalog Number:** CPO1000-0-25  
**Product ID:** 7TAA017300R0237  
**UPC Number:** 78621085132  
**Status:** A



Thin-Wall Heat Shrinkable Tubing, Black Cross-Linked Polyolefin, 1 Inch, Shrink Ratio 2:1, Length 25-Foot Reel, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&#amp;2; AMS 3636 &#amp;2; 3637; DEF STAN 59-97, Issue 3, Type 2a

Actual

### North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Voltage Rating	600 V
Thickness	Thin
Length	25 ft
Color	Black

### European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	25.4mm
Inner diameter after heat-shrink	12.7mm
Nominal diameter inch	1 inch
Wall thickness after shrinking	10.16mm
Length	7.62m
Operation temperature	-55-+135°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

### Packaging

Inner Quantity	1
Outer Quantity	10
Outer Dimensions (inches)	13.4x13x6.6
Weight Uom	106 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2