

Catalog Number: CPO250-2-A
Product ID: 7TAA017310R0125
UPC Number: 78621083424
Status: A



Actual

Thin-Wall Heat Shrinkable Tubing, Red Cross-Linked Polyolefin, 1/4 Inch, Shrink Ratio 2:1, Length 4 Feet, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

North American Specifications (UNSPSC)

| | |
|------------------|---|
| UNSPSC | 39121723 Heat shrinkable tube |
| IGCC | 5073 Heat shrinkable tube |
| Type | Thin-Wall Heat Shrinkable Tubing |
| Special Features | Flame-retardant, cross-linked polyolefin. |
| Shrink Ratio | 2:1 |
| Thickness | Thin |
| Length | 4 ft |
| Color | Red |

European Specifications (ETIM)

| | |
|-----------------------------------|------------------------|
| ETIM | EC000217 Shrink tubing |
| Type | Heat-shrink |
| Model | Thin-walled |
| Shrink rate | 2:1 |
| Inner diameter before heat-shrink | 6.35mm |
| Inner diameter after heat-shrink | 3.302mm |
| Nominal diameter inch | 1/4 inch |
| Wall thickness after shrinking | 0.508mm |
| Length | 1.22m |
| Operation temperature | -55-+135°C |
| Colour | Red |
| Material | Polyolefin (PO-X) |
| Halogen free | N |
| With inner glue | N |
| Printable | N |
| UL approval | Y |

Packaging

| | |
|---------------------------|-----------------|
| Inner Quantity | 25 |
| Inner Dimensions (inches) | 1x1x1 |
| Outer Quantity | 250 |
| Outer Dimensions (inches) | 50x10x8 |
| Weight Uom | 26 lbs. per 100 |

Documents / Support Tools

| | |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
| Catalog Page | Available on Website |