



**Catalog Number:** CPO-A-750-48  
**Product ID:** 7TAA017320R0032  
**UPC Number:** 78621024736  
**Status:** A



Thin-Wall Heat Shrinkable Tubing, Black Polyolefin, 3/4 Inch, Shrink Ratio 3:1, Length 48 Inches, Operating Temperature -55 to 110 Degrees Celsius, Adhesive Lined

- Adhesive lined for moisture-proof environmental seal.
- High 3:1 shrink ratio for covering irregularly shaped objects.

Actual

**North American Specifications (UNSPSC)**

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Adhesive lined for moisture-proof environmental seal.
Voltage Rating	600 V
Thickness	Thin
Length	4 ft
Color	Black

**European Specifications (ETIM)**

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	3:1
Inner diameter before heat-shrink	19.05mm
Inner diameter after heat-shrink	7.874mm
Nominal diameter inch	3/4 inch
Wall thickness after shrinking	1.778mm
Length	1.22m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

**Packaging**

Outer Quantity	25
Outer Dimensions (inches)	50x15x8.5
Weight Uom	16.81 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2