

Catalog Number: CPO187-0-C
Product ID: 7TAA017310R0079
UPC Number: 78621083386
Status: A



Thin-Wall Heat Shrinkable Tubing, Black Cross-Linked Polyolefin, 3/16 Inch, Shrink Ratio 2:1, Length 100 Feet, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&#amp;2; AMS 3636 &#amp;2; 3637; DEF STAN 59-97, Issue 3, Type 2a

Actual

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Voltage Rating	600 V
Thickness	Thin
Length	100 ft
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	4.826mm
Inner diameter after heat-shrink	2.286mm
Nominal diameter inch	3/16 inch
Wall thickness after shrinking	0.508mm
Length	30.48m
Operation temperature	-55-+135°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	16x6.75x16
Weight Uom	1.93 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website