



Actual

**Catalog Number:** CPO187-C-25  
**Product ID:** 7TAA017310R0099  
**UPC Number:** 78621085116  
**EAN Number:** 05415022255676  
**Status:** A

Thin-Wall Heat Shrinkable Tubing, Clear Cross-Linked Polyolefin, 3/16 Inch, Shrink Ratio 2:1, Length 25-Foot Reel, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

### North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Voltage Rating	600 V
Thickness	Thin
Length	25 ft
Color	Transparent

### European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	4.826mm
Inner diameter after heat-shrink	2.286mm
Nominal diameter inch	3/16 inch
Wall thickness after shrinking	0.508mm
Length	7.62m
Operation temperature	-55-+135°C
Colour	Transparent
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	N

### Packaging

Inner Quantity	1
Outer Quantity	10
Outer Dimensions (inches)	13.5x13.25x6.5
Weight Uom	32 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2