



Catalog Number: 696-41848
Product ID: 7TAG009520R0035
UPC Number: 78621090316
EAN Number: 05414363011378
Status: A



Actual

Panel and Chassis Mounting Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 317.5mm (12.5 Inches), Width of 5.59mm (0.22 Inches), Thickness of 1.65mm (0.65 Inches), Tensile Strength Rating of 289 Newtons (65 Pounds), Mounting Hole Size of 8.13 - 17.27mm (0.32 - 0.68 Inches)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Panel and Chassis Mounting
Width	0.22 in ; 5.59 mm
Length	12.5 in ; 317.5 mm
Thickness	0.06 in ; 1.65 mm
Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	65 pounds ; 289 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	5.59mm
Length belt/tape/tie	317.5mm
Tie thickness	1.65mm
Min. holding force	289N
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	500
Outer Quantity	1000
Outer Dimensions (inches)	20.8x13.1x9.1
Weight Uom	9.38 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000559
Instruction Sheet	TA01182-TB2

