



Actual

Catalog Number: TY46M
Product ID: 7TAG009510R0018
UPC Number: 78621082513
EAN Number: 05414363064831
Status: A

Identification Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 184.15mm (7.25 Inches), Width of 4.81mm (0.19 Inches), Thickness of 1.41mm (0.055 Inches), Tensile Strength Rating of 220 Newtons (50 pounds), Marking Pad Size of 12.7mm (0.50 Inches) x 26.99mm (1.062 Inches), Military Specified (MIL-SPEC MS3368-1-9), Bulk Pack

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5040 I.D. Ties
Type	Identification
Standard	UL E49405
Width	0.189 in ; 4.8 mm
Length	7.24 in ; 184 mm
Thickness	0.055 in ; 1.4 mm
Bundle Diameter	0.37 to 1.77 in ; 9.5 to 45 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds ; 220 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.81mm
Length belt/tape/tie	184.15mm
Tie thickness	1.41mm
Max. bundle diameter	45mm
Min. holding force	220N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	Adjacent to bundle
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

Packaging

Inner Quantity	1000
Outer Quantity	10000
Outer Dimensions (inches)	21.2x13.7x9.6
Weight Uom	2.35 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US
Catalog Page

Available on Website
Available on Website
