



Actual

Catalog Number: TY51M
Product ID: 7TAG009510R0046
UPC Number: 78621082529
EAN Number: 05414363065180
Status: A

Identification Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 91mm (3.6 Inches), Width of 2.54mm (1 Inch), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), Marking Pad Size of 25.4mm (1.0 Inch) x 7.95mm (0.313 Inch), Military Specified (MIL-SPEC MS3368-5-E)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5040 I.D. Ties
Type	Identification
Standard	UL E49405
Width	0.1 in ; 2.54 mm
Length	3.6 in ; 91 mm
Thickness	0.04 in ; 1 mm
Bundle Diameter	0.39 to 0.63 in ; 10 to 16 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds ; 80 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.3mm
Length belt/tape/tie	91mm
Tie thickness	1mm
Max. bundle diameter	16mm
Min. holding force	80N
Operating temperature	-60-+85°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	Adjacent to bundle
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

Packaging

Inner Quantity	500
Inner Dimensions (inches)	8.2x4.9x3.6
Outer Quantity	5000
Outer Dimensions (inches)	10.7x10.2x9.3
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

