



Catalog Number: TYZ523M
Product ID: 7TAG009620R0006
UPC Number: 78621077043
EAN Number: 05414363068167
Status: A



High Performance Cable Tie, Aquamarine Fluoropolymer ETFE for Temperatures up to 150 Degrees Celsius (302 F), Length of 91mm (3.6 Inches), Width of 2.5mm (0.1 Inch), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), 100 Pack

- Application Tool: ERG50/1-3

Actual

North American Specifications (UNSPSC)

| | |
|------------------|---------------------------------|
| UNSPSC | 39121703 Cable ties |
| IGCC | 5034 Cable ties |
| Type | Radiation Resistant |
| Standard | UL E49405, CSA 2884 |
| Width | 0.1 in ; 2.5 mm |
| Length | 3.6 in ; 91 mm |
| Thickness | 0.04 in ; 1 mm |
| Bundle Diameter | 0.1 to 0.62 in ; 2.5 to 15.8 mm |
| Material | Fluoropolymer ETFE |
| Color | Aqua |
| Lock Mechanism | Stainless Steel Barb |
| Tensile Strength | 18 pounds ; 80 newtons |

European Specifications (ETIM)

| | |
|---------------------------|--------------------|
| ETIM | EC000046 Cable tie |
| Band width | 2.5mm |
| Length belt/tape/tie | 91mm |
| Tie thickness | 1mm |
| Max. bundle diameter | 15.8mm |
| Min. holding force | 80N |
| Operating temperature | -45-+150°C |
| Model | Internal toothing |
| Band closure | Steel nose |
| Material | Plastic |
| Material quality | Other |
| Surface protection | Untreated |
| UV-stable acc. ASTM D6779 | N |
| Halogen free | N |
| Colour | Other |
| Transparent | N |
| Reflective (fluorescent) | N |
| Text strip | None |
| Solvable fastener | N |
| VG approval | N |
| MIL approval | N |
| UL approval | Y |

Packaging

| | |
|---------------------------|--------------------|
| Inner Quantity | 100 |
| Inner Dimensions (inches) | 7x3.5x0 |
| Outer Quantity | 500 |
| Outer Dimensions (inches) | 12.8x10.5x10.7 |
| Weight Uom | 1.25 lbs. per 1000 |

Documents / Support Tools



Technical Drawing / Data Sheet US

Available on Website