



Actual

Catalog Number: TYZ525M
Product ID: 7TAG009620R0007
UPC Number: 78621077044
EAN Number: 05414363068174
Status: A

High Performance Cable Tie, Aquamarine Fluoropolymer ETFE for Temperatures up to 150 Degrees Celsius (302 F), Length of 185mm (7.3 Inches), Width of 4.1mm (0.2 Inch), Thickness of 1.6mm (0.06 Inch), Tensile Strength Rating of 222 Newtons (50 Pounds), 100 Pack

- Application Tool: ERG50-6-8

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Radiation Resistant
Standard	UL E49405
Width	0.2 in ; 4.1 mm
Length	7.3 in ; 185 mm
Thickness	0.06 in ; 1.6 mm
Bundle Diameter	0.25 to 1.75 in ; 6.4 to 44.5 mm
Material	Fluoropolymer ETFE
Color	Aqua
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds ; 222 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.1mm
Length belt/tape/tie	185mm
Tie thickness	1.6mm
Max. bundle diameter	44.5mm
Min. holding force	222N
Operating temperature	-45-+150°C
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Other
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	N
Colour	Other
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	100
Inner Dimensions (inches)	12x6x0
Outer Quantity	500
Outer Dimensions (inches)	10x4.3x6.3
Weight Uom	5.63 lbs. per 1000

Documents / Support Tools



Technical Drawing / Data Sheet US

[Available on Website](#)