


GALVANIZED LOW PROFILE 90° SELF DUMPING HOPPER - H-100-HD-GAL

APPROX WEIGHT: 454.54 lbs.
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

WARNING THIS PRODUCT CAN EXPOSE YOU TO LEAD, WHICH IS KNOWN TO THE STATE OF CALIFORNIA TO CAUSE CANCER AND BIRTH DEFECTS OR OTHER REPRODUCTIVE HARM. FOR MORE INFORMATION GO TO www.p65warnings.ca.gov



NEVER EXCEED LOAD CENTER RATING PER FORK TRUCK MANUFACTURER'S GUIDELINES. DO NOT USE THIS FORK TRUCK ATTACHMENT IF LOAD WILL EXCEED FORK TRUCK MANUFACTURER'S LOAD CENTER RATING.

APPROX. WEIGHT/ LOST LOAD=454.54 LBS.

EFFECTIVE THICKNESS= FORK LENGTH MINUS 21 3/4"


**** ADDITION OF CASTERS MAY CHANGE WEIGHT CAPACITY BASED ON CASTER RATING**

STANDARD FEATURES

MODEL NUMBER: H-100-HD-GAL
OVERALL WIDTH: 51"
OVERALL LENGTH: 51 1/4"
OVERALL HEIGHT: 28 3/16"
CAPACITY: 6,000 LBS.
VOLUME: 1 CU. YRD.
FINISH: HOT DIP GALVANIZED

SPECIAL FEATURES

NONE



APPROVAL	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.	
	ANY MODIFIED UNITS ARE NON-RETURNABLE	
<input type="checkbox"/> As drawn <input type="checkbox"/> As marked		
Signed: _____ Date: _____		
Printed Name: _____		
LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING		

FOR INTERNAL USE ONLY PROJECT SIGN OFF		DISTRIBUTOR'S NAME: VESTIL MANUFACTURING		P.O.# <input checked="" type="checkbox"/> X
SALES		DRAWN BY: SJG	DATE: 2/12/2018	W.O.# <input checked="" type="checkbox"/> X
ENG.		REFERENCE: X	SCALE: 1:16	SALES: <input checked="" type="checkbox"/> X
FAB.		QUOTED LEAD TIME: X	QUOTE # X	FILE NAME: 37-007-139
POWER				