



Dealers Industrial Equipment

No.:

Date: 13-SEP-2016

DATA SHEET Single-phase induction motor - Squirrel cage rotor

Customer :
 Product line : Single Phase: W01 (Rolled Steel) - ODP - Premium Efficiency (DOE)

Frame : 56H
 Output : 3 HP
 Frequency : 60 Hz
 Poles : 2
 Full load speed : 3500 rpm
 Slip : 2.78 %
 Voltage : 115/208-230 V
 Rated current : 24.4/13.5-12.2 A
 Locked rotor current : 200/100 A
 Locked rotor current (I_L/I_n) : 8.2
 No-load current : 7.80/3.90 A
 Full load torque : 4.44 lb.ft
 Locked rotor torque : 220 %
 Breakdown torque : 280 %
 Design : ---
 Insulation class : F
 Temperature rise : 80 K
 Locked rotor time : 6 s (hot)
 Service factor : 1.15
 Duty cycle : S1
 Ambient temperature : -20°C - +40°C
 Altitude : 1000 m
 Degree of Protection : ODP
 Approximate weight : 42 lb
 Moment of inertia : 0.09445 sq.ft.lb
 Noise level : 58 dB(A)

	D.E.	N.D.E.
Bearings	6204 ZZ	6202 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.93	84.1
75%	0.92	81.0
50%	0.87	76.0

Notes:
 Downloaded from <http://dealerselectric.com>
 Generated for Model #00336OT1B56CFL-S

Performed by

Checked