



Dealers Industrial Equipment

No.:

Date: 13-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Oil Well Pumping : High Slip - NEMA Design "D" - ODP

Frame : 256T
Output : 10 HP
Frequency : 60 Hz
Poles : 6
Full load speed : 1110 rpm
Slip : 7.50 %
Voltage : 208-230/460 V
Rated current : 29.9-27.0/13.5 A
Locked rotor current : 162/81.0 A
Locked rotor current (I_L/I_n) : 6.0
No-load current : 13.8/6.90 A
Full load torque : 46.7 lb.ft
Locked rotor torque : 300 %
Breakdown torque : 0 %
Design : D
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 9 s (hot)
Service factor : 1.00
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP23
Approximate weight : 265 lb
Moment of inertia : 3.4086 sq.ft.lb
Noise level : 57 dB(A)

	D.E.	N.D.E.
Bearings	6309 C3	6209 C3
Regreasing interval	20000 h	20000 h
Grease amount	13 g	9 g

Load	Power factor	Efficiency (%)
100%	0.84	83.0
75%	0.78	84.0
50%	0.65	83.0

Notes:

Downloaded from <http://dealersselectric.com>
Generated for Model #01012OS3EOW256T

Performed by

Checked