



Dealers Industrial Equipment

No.:

Date: 23-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Three-Phase : Explosion Proof - NEMA Premium

Frame : 254T
Output : 15 HP
Frequency : 60 Hz
Poles : 4
Full load speed : 1770 rpm
Slip : 1.67 %
Voltage : 208-230/460 V
Rated current : 40.7-36.8/18.4 A
Locked rotor current : 269/134 A
Locked rotor current (I_L/I_N) : 7.3
No-load current : 17.2/8.60 A
Full load torque : 43.9 lb.ft
Locked rotor torque : 300 %
Breakdown torque : 300 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 26 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 329 lb
Moment of inertia : 2.3111 sq.ft.lb
Noise level : 69 dB(A)

	D.E.	N.D.E.
Bearings	6309 2RS-C3	6209 2RS-C3
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.81	92.4
75%	0.75	91.7
50%	0.65	90.2

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #01518XT3E254T

Performed by

Checked