



Dealers Industrial Equipment

No.:

Date: 23-SEP-2016

### DATA SHEET Three-phase induction motor - Squirrel cage rotor

Customer :  
Product line : W01 (Rolled Steel) General Purpose ODP

Frame : 213/5T  
Output : 15 HP  
Frequency : 60 Hz  
Poles : 2  
Full load speed : 3535 rpm  
Slip : 1.81 %  
Voltage : 208-230/460 V  
Rated current : 38.0-34.4/17.2 A  
Locked rotor current : 237/119 A  
Locked rotor current (I<sub>L</sub>/I<sub>n</sub>) : 6.9  
No-load current : 12.3/6.17 A  
Full load torque : 22.0 lb.ft  
Locked rotor torque : 210 %  
Breakdown torque : 280 %  
Design : B  
Insulation class : F  
Temperature rise : 80 K  
Locked rotor time : 8 s (hot)  
Service factor : 1.15  
Duty cycle : S1  
Ambient temperature : -20°C - +40°C  
Altitude : 1000 m  
Degree of Protection : ODP  
Approximate weight : 131 lb  
Moment of inertia : 0.55125 sq.ft.lb  
Noise level : 66 dB(A)

	D.E.	N.D.E.
Bearings	6208 ZZ	6206 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.89	90.2
75%	0.86	90.2
50%	0.77	90.2

Notes:  
Downloaded from <http://dealerselectric.com>  
Generated for Model #01536OT3E215T-SG

Performed by

Checked