



Dealers Industrial Equipment

No.:

Date: 23-SEP-2016

DATA SHEET Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : W22 Super Premium

Frame : 284/6T
 Output : 30 HP
 Frequency : 60 Hz
 Poles : 4
 Full load speed : 1775 rpm
 Slip : 1.39 %
 Voltage : 208-230/460 V
 Rated current : 78.7-71.2/35.6 A
 Locked rotor current : 570/285 A
 Locked rotor current (I_L/I_n) : 8.0
 No-load current : 34.0/17.0 A
 Full load torque : 87.6 lb.ft
 Locked rotor torque : 320 %
 Breakdown torque : 350 %
 Design : A
 Insulation class : F
 Temperature rise : 80 K
 Locked rotor time : 25 s (hot)
 Service factor : 1.25
 Duty cycle : S1
 Ambient temperature : -20°C - +40°C
 Altitude : 1000 m
 Degree of Protection : IP55
 Approximate weight : 450 lb
 Moment of inertia : 5.6660 sq.ft.lb
 Noise level : 64 dB(A)

	D.E.	N.D.E.
Bearings	6311 C3	6211 C3
Regreasing interval	20000 h	20000 h
Grease amount	18 g	11 g

Load	Power factor	Efficiency (%)
100%	0.82	94.5
75%	0.76	94.1
50%	0.64	93.0

Notes:
 Downloaded from <http://dealerselectric.com>
 Generated for Model #03018EG3E286T-W22

Performed by

Checked